

系列名 Series Name

## RMD-L

电机简称 Motor Simplified Name


L-4015



### 单编码器 Single Encoder

型号 Actuator Full Name	通信方式 Communication	货品编码 Product Code
RMD-L-4015-100-C	CAN	110102082006
RMD-L-4015-100-R	RS485	110102082005

## 尺寸安装图 Installation Drawing



## 产品参数 Product Parameters

产品名称 Item Name	L-4015	
额定电压 Nominal Voltage	V	12~24
额定电流 Nominal Current	A	1.88
额定扭矩 Nominal Torque	N.M	0.22
额定转速 Nominal Speed	RPM	520
最大空载转速 Max Speed	RPM	1010
最大瞬时扭矩 Max Instant Torque	N.M	0.49
最大瞬时电流Max Instant Current	A	4.3
线电阻 Line Resistance	Ω	3.3
接线方式 Wire Connect	-	Y
相间电感 Phase to Phase Inductance	mH	0.78
转速常数 Speed Constant	RPM/V	63
扭矩常数 Torque Constant	N.M/A	0.12
转子惯量 Rotor Inertia	gcm²	105
极对数 Number of Pole Pairs	-	13
电机重量 Motor Weight	g	120
工作温度范围 Working Temperature	℃	(-20 ~ 80 ℃)
最高退磁温度 Max Demagnetize Temperature	℃	120 ℃
控制精度 Control Precision	°	0.001°

### 适配驱动器 Matched Driver

适配驱动类型 Drive	-	MC100
驱动器输入电压范围 Input Voltage	V	12~24
驱动器电流范围 Current	A	Normal:5A Instant:8A
额定功率 Normminal Power	W	100
编码器精度 Encoder	-	18-bit magnetic encoder
通信方式及波特率 Communication method and baud rate	-	CAN BUS :1M ; RS485: 115200/500k/1M/2.5M
控制模式 control mode	-	Torque loop(current loop) / speed loop/position loop
加速度曲线 S-Curve	-	YES

## 电机特征曲线 Motor Characteristic Curve

