

系列名 Series Name

RMD-L

电机简称 Motor Simplified Name


L-9025



单编码器 Single Encoder

型号 Actuator Full Name	通信方式 Communication	货品编码 Product Code
RMD-L-9025-200-C	CAN	110105033506
RMD-L-9025-200-R	RS485	110105033505

## 尺寸安装图 Installation Drawing



## 产品参数 Product Parameters

产品名称 Item Name	L-9025	
额定电压 Nominal Voltage	V	12~24
额定电流 Nominal Current	A	3.46
额定扭矩 Nominal Torque	N.M	2.79
额定转速 Nominal Speed	RPM	130
最大空载转速 Max Speed	RPM	280
最大瞬时扭矩 Max Instant Torque	N.M	5.8
最大瞬时电流Max Instant Current	A	7.6
线电阻 Line Resistance	Ω	1.9
接线方式 Wire Connect	-	Y
相间电感 Phase to Phase Inductance	mH	4.71
转速常数 Speed Constant	RPM/V	12
扭矩常数 Torque Constant	N.M/A	0.76
转子惯量 Rotor Inertia	gcm <sup>2</sup>	4656
极对数 Number of Pole Pairs	-	14
电机重量 Motor Weight	g	880
工作温度范围 Working Temperature	℃	(-20 ~ 80 ℃)
最高退磁温度 Max Demagnetize Temperature	℃	120 ℃
控制精度 Control Precision	°	0.001°

## 适配驱动器 Matched Driver

适配驱动器 Matched Driver	适配驱动器 Matched Driver
适配驱动类型 Drive	- MC200
驱动器输入电压范围 Input Voltage	V 12~24
驱动器电流范围 Current	A Normal:8A Instant:15A
额定功率 Normminal Power	W 200
编码器精度 Encoder	- 14-bit magnetic encoder
通信方式及波特率 Communication method and baud rate	- CAN BUS :1M ; RS485: 115200/500k/1M/2.5M
控制模式 control mode	- Torque loop(current loop) / speed loop/position loop
加速度曲线 S-Curve	YES

## 电机特征曲线 Motor Characteristic Curve

